# TECHNICAL DATA SHEET



<24 hr hrs

20

0.3 N/mm2 / 44 psi

# **MM709** 2 part moulding compound

**Uncured Product** 

Description **Test Method Property** 

This is a two-component low tear room temperature condensation cure silicone system. The cured rubber is suitable for the mould making of patterns with fine details, where some dimensional stability is required. Low tear silicone moulding rubbers are cost effective for the production of moulds only requiring a few impressions. They find uses in the reproduction of plane surface objects

## **Key Features**

- Very soft moulding rubber
- Suitable for tampon print pads
- Easily degassed
- Low viscosity

#### **Application**

Printing pads

#### **Use and Cure Information**

The curing process starts as soon as the catalyst is added. Under normal conditions of temperature and humidity typical curing characteristics are described below. If the product is to be used in contact with aggressive chemicals, such as high styrene polyester resins or epoxies, it is recommended that the rubber be allowed to cure for 48 hours before use.

Pour the catalysed rubber into the mould from one point, ensuring air is not entrapped. Allow the rubber to cure before removing from the mould. To allow the rubber to achieve its maximum physical properties and chemical resistance leave the partially cured rubber to age at room temperature for at least a further 12 hours.

#### How to Use

Charge the base rubber into a clean plastic or metal container, approximately 3-4 times its volume.

Add standard catalyst in the proportion of 5 parts by weight of catalyst to 100 parts by weight of the rubber base. Mix thoroughly, slowly at first to avoid splashing and taking care to avoid excessive air entrapment. After catalysation any entrapped air may be removed by intermittent evacuation for several minutes. The use of a sufficiently large container permits degassing without overflow.

Value

Viscous liquid Appearance Color A **Translucent** 23°C and 50% Cure Profile humidity Cure Type Condensation

De-mould Time / Full Cure at

23°C/73°F Mix Ratio By Weight 20:1

>45 min mins Pot Life mins at 23°C/73°F Liquid Rheology

Brookfield 18000 cP Viscosity A Viscosity B Brookfield 50 cP

### **Cured Product**

CTE Volumetric ppm/°C 930 ppm/°C Color Blue Density BS ISO 2781 1.00 g/cm3 Elongation at Break **ISO 37** 600 % ASTM D 2240-

Hardness Shore 00 95

Linear Coefficient of Thermal 310 ppm/°C Expansion (ppm/°C)

Linear Shrinkage (%) 0.5 %

Max Working Temp 180 °C / 356 °F Min Working Temp -50 °C / -58 °F BS ISO 34-1 Tear Resistance (N/mm) 3 N/mm / 17 ppi

**ISO 37** 

Storage

Tensile Strength

40 °C / 104 °F Max Storage Temperature Shelf Life 12 mths

# Catalysts

Use the following catalysts:

Code	Colour	Pot Life	De-Mould
MM CAT L5 NT		>60 mins	<24 hrs

## **Health & Safety**

### **Health and Safety**

Safety Data Sheets available on request.

### **Packaging**

CHT Moulding Rubbers are available in a variety packaging including bulk containers. Please contact our sales department for more information.

**Revision Date** 20 May 2021

Revision No

**Download Date** 18 May 2024

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.